



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Female-Male, Tapping "Tee", 300/400, 600V AC/DC, Single Conductor, Pre-Wired, Brown



By Bryant
Catalog # HBLTBN

Heavy Duty Single Pole Industrial Grade, Female-Female-Male, Tapping "Tee", 300/400,600V AC/DC, Single Conductor, Pre-Wired

Features

- Industrial Grade
- Female-Female-Male
- Tapping "Tee"

Application

High Ampacity

Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of the device

General

Catalog Number	HBLTBN
Color	Brown
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	T-Fittings
Material	Brass and Elastomer
Number Of Pins	1) In, 2) Out- Male-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Series 16
Specifications	<ul style="list-style-type: none"> • Body Material - Thermoplastic Elastomer

- Contact Material - Brass
- Product Type - T's" and Tri-Taps
- Tee and Tap Type - "T" Fitting

Style	Tapping Tee Female-Female-Male
Type	Tees and 3-Fers
UPC	783585113180

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK H-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBLTBN](#)