



# Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Female-Male, Tapping "Tee", 300/400A 600V AC/DC, Single Conductor, Pre-Wired, Green

By Bryant  
Catalog # HBLTGN



Heavy Duty Single Pole Industrial Grade, Female-Female-Male, Tapping "Tee", 300/400A 600V AC/DC, Single Conductor, Pre-Wired

## Application

High Ampacity

## General

Color	Green
Insulation	Insulated Body
Item Type	T-Fittings
Material	Brass and Elastomer
Number Of Pins	1) In, 2) Out- Male-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Amperage Rating - 400A Maximum</li> <li>• Electrical - Voltage Ratings - 600V AC Maximum</li> <li>• 250V DC Maximum</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> </ul>
Series	Series 16
Style	Tapping Tee Female-Female-Male
Type	Tees and 3-Fers
UPC	783585174204

## Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

## Certifications and Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - Bryant L-7 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.