



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20' Length, Black

By Bryant
Catalog # [HC5EBK20](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20' Length, Black

General

| | |
|-----------------------|---|
| Attenuation | .1dB |
| Boot Type | PVC |
| Color | Black |
| EU RoHS Indicator | Yes |
| Item Type | NEXTSPEED Category 6 and 5e Patch Cords |
| Material - Insulation | Flame Redardant PVC |
| Material - Jacket | Flame Redardant PVC |
| Performance | <ul style="list-style-type: none">Mechanical - Cable to plug tensile strength - 20+ lbs.Mechanical - Mating Cycles - 2000+ |
| Plug Type | RJ45 |
| Temperature Rating | Per TIA |
| Type | Standard |
| UPC | 662620234304 |

Dimensions

| | |
|------------------|-------|
| Length | 20 ft |
| Outside Diameter | 0.218 |

Electrical Ratings

| | |
|----------------|------------|
| Voltage Rating | 300V AC kV |
|----------------|------------|

Conductor Related

| | |
|----------------------|-------------|
| Conductor Stranding | Stranded |
| Conductor Type | Copper |
| Number Of Conductors | 8-Conductor |
| Wire Size | #24 AWG |

Certifications and Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">ANSI/TIA/EIA-568-C.2 Category 5E ComponentISO 11801/60603-7-41 Category 5E Component |
|----------------------|---|

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HC5EBK20-SPEC-EN | REV 7/2023