



Patch Cord, Speed Gain, Cat5E, Slim, Gray, 10'

By Bryant
Catalog # [HC5EGY07](#)



Patch Cord, Speed Gain, Cat5E, Slim, Gray, 10'

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Color	<ul style="list-style-type: none">• Gray• Gris
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none">• Mechanical - Cable to plug tensile strength - 20+ lbs.• Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	<ul style="list-style-type: none">• Standard• Standard
UPC	662620234960

Dimensions

Length	7 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 5E Component• ISO 11801/60603-7-41 Category 5E Component
----------------------	---

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HC5EGY07-SPEC-EN | REV 7/2023