

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 15' Length, Orange

By Bryant
Catalog # [HC5EOR15](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 15' Length, Orange

Features

-
-
-
-

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EOR15
Color	Orange
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	<ul style="list-style-type: none">• Conductor - 24AWG UTP• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating• Jacket - Flame-Retardant PVC-CM Rated• Plug Body - Polycarbonate UL 94V-0

Temperature Rating	• Plug Boot - Polycarbonate UL 94V-0
Type	Per TIA Standard
UPC	662620235219

Dimensions

Length	15 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 5E Component• ISO 11801/60603-7-41 Category 5E Component
----------------------	---

Product Assets

[Specifications - HC5EOR15](#)