



# Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Orange



By Bryant  
Catalog # [HC5EOR25](#)

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Orange

## Features

- 
- 
- 
- 

## Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

## General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EOR25
Color	Orange
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	<ul style="list-style-type: none"> <li>• Conductor - 24AWG UTP</li> <li>• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating</li> <li>• Jacket - Flame-Retardant PVC-CM Rated</li> <li>• Plug Body - Polycarbonate UL 94V-0</li> </ul>

Temperature Rating	• Plug Boot - Polycarbonate UL 94V-0
Type	Per TIA Standard
UPC	662620235233

## Dimensions

Length	25 ft
Outside Diameter	0.218

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• ANSI/TIA/EIA-568-C.2 Category 5E Component</li> <li>• ISO 11801/60603-7-41 Category 5E Component</li> </ul>
----------------------	------------------------------------------------------------------------------------------------------------------------------------------------------

## Product Assets

[Specifications - HC5EOR25](#)