



# Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 3' Length, Pink



By Bryant

Catalog # [HC5EPK03](#)

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 3' Length, Pink

## Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

## Application

Category 5e

## General

|                       |                                         |
|-----------------------|-----------------------------------------|
| Attenuation           | .1dB                                    |
| Boot Type             | PVC                                     |
| Catalog Number        | HC5EPK03                                |
| Color                 | Pink                                    |
| EU RoHS Indicator     | Yes                                     |
| Item Type             | NEXTSPEED Category 6 and 5e Patch Cords |
| Material - Insulation | Flame Redardant PVC                     |
| Material - Jacket     | Flame Redardant PVC                     |

|                    |              |
|--------------------|--------------|
| Plug Type          | RJ45         |
| Temperature Rating | Per TIA      |
| UPC                | 662620235639 |

## Dimensions

|                  |       |
|------------------|-------|
| Outside Diameter | 0.218 |
|------------------|-------|

## Electrical Ratings

|                |            |
|----------------|------------|
| Voltage Rating | 300V AC kV |
|----------------|------------|

## Conductor Related

|                      |             |
|----------------------|-------------|
| Conductor Stranding  | Stranded    |
| Conductor Type       | Copper      |
| Number of Conductors | 8-Conductor |
| Wire Size            | #24 AWG     |

## Product Assets

[Specifications - HC5EPK03](#)