



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 5' Length, Pink



By Bryant

Catalog # [HC5EPK05](#)

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 5' Length, Pink

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Application

Category 5e

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EPK05
Color	Pink
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC

Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620235646

Dimensions

Outside Diameter	0.218
------------------	-------

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

[Specifications - HC5EPK05](#)



A Hubbell brand