



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 10' Length, Pink

By Bryant
Catalog # [HC5EPK10](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 10' Length, Pink

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Application

Category 5e

General

| | |
|-----------------------|---|
| Attenuation | .1dB |
| Boot Type | PVC |
| Color | Pink |
| EU RoHS Indicator | Yes |
| Item Type | NEXTSPEED Category 6 and 5e Patch Cords |
| Material - Insulation | Flame Redardant PVC |
| Material - Jacket | Flame Redardant PVC |
| Plug Type | RJ45 |
| Temperature Rating | Per TIA |
| UPC | 662620235660 |

Dimensions

Outside Diameter 0.218

Electrical Ratings

Voltage Rating 300V AC kV

Conductor Related

| | |
|----------------------|-------------|
| Conductor Stranding | Stranded |
| Conductor Type | Copper |
| Number Of Conductors | 8-Conductor |
| Wire Size | #24 AWG |

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HC5EPK10-SPEC-EN | REV 7/2023