



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20' Length, Yellow

By Bryant
Catalog # [HC5EY20](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20' Length, Yellow

Features

-
-
-
-

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EY20
Color	Yellow
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	Mechanical - Cable to plug tensile strength - 20+ lbs. Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620236773

Dimensions

Length	20 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568-C.2 Category 5E Component ISO 11801/60603-7-41 Category 5E Component
----------------------	---

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-HC5EY20-SPEC-EN | REV 6/2024