



# Patch Cord, Speed Gain, Cat6, Slim, Blue, 20'

By Bryant  
Catalog # [HC6B20](#)



Patch Cord, Speed Gain, Cat 6,Slim, 20'

## General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6B20
Color	Blue
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	Mechanical - Cable to plug tensile strength - 20+ lbs. Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
	Standard
UPC	662620231549

## Dimensions

Length	20 ft
Outside Diameter	0.218

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

## Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568-C.2 Category 6 Component ISO 11801/60603-7-41 Category 6 Component
----------------------	---

## Logistics

Carton Quantity	15
Pallet Quantity	810

## Product Assets

- [Catalog Page - PREM D5 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY-HC6B20-SPEC-EN | REV 6/2024