



# Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 1' Length, Black

By Bryant  
Catalog # [HC6BK01](#)



Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 1' Length, Black

## Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

## General

Attenuation	.1dB
Boot Type	PVC
Color	Black
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none"><li>• Mechanical - Cable to plug tensile strength - 20+ lbs.</li><li>• Mechanical - Mating Cycles - 2000+</li></ul>
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620231716

## Dimensions

Length	1 ft
Outside Diameter	0.218

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• ANSI/TIA/EIA-568-C.2 Category 6 Component</li><li>• ISO 11801/60603-7-41 Category 6 Component</li></ul>
----------------------	---

## Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-HC6BK01-SPEC-EN | REV 7/2023