



# Patch Cord, Speed Gain, Cat6, Slim, Black, 3'

By Bryant  
Catalog # [HC6BK03](#)



Patch Cord, Speed Gain, Cat6, Slim, Black, 3'

## Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

## General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6BK03
Color	Black
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	Mechanical - Cable to plug tensile strength - 20+ lbs. Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620231723

## Dimensions

Length	3 ft
Outside Diameter	0.218

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

## Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568-C.2 Category 6 Component ISO 11801/60603-7-41 Category 6 Component
----------------------	---

## Logistics

Carton Quantity	65
Pallet Quantity	3510

## Product Assets

[Catalog Page - PREM D5 CatalogPage](#)  
[Catalogs - Premise Wiring Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-HC6BK03-SPEC-EN | REV 6/2024