



# Patch Cord, Speed Gain, Cat6, Slim, Green, 7'

By Bryant  
Catalog # [HC6GN07](#)



Patch Cord, Speed Gain, Cat6, Slim, Green, 7'

## General

Attenuation	.1dB
Boot Type	PVC
Color	Green
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none"><li>Mechanical - Cable to plug tensile strength - 20+ lbs.</li><li>Mechanical - Mating Cycles - 2000+</li></ul>
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620232201

## Dimensions

Length	7 ft
Outside Diameter	0.218

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>ANSI/TIA/EIA-568-C.2 Category 6 Component</li><li>ISO 11801/60603-7-41 Category 6 Component</li></ul>
----------------------	---

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets



A proud member of the Hubbell Family.