



Patch Cord, Speed Gain, Cat6, Slim, Red, 7'

By Bryant
Catalog # [HC6R07](#)



Patch Cord, Speed Gain, Cat 6,Slim, 7'

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6R07
Color	<ul style="list-style-type: none"> • Red •
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating Type	Per TIA <ul style="list-style-type: none"> • Standard • Standard
UPC	662620233352

Dimensions

Length	7 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • ANSI/TIA/EIA-568-C.2 Category 6 Component • ISO 11801/60603-7-41 Category 6 Component
----------------------	--

Product Assets

- [Catalog Page - PREM D5 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)