



Cable Assembly, HDMI, #24 AWG, Coupler, Black, 30' Length

By Bryant
Catalog # [HDC30BK](#)



Cable Assembly, HDMI, #24 AWG, Coupler, Black, 30' Length

Application

1080P HD Video

General

Braid	Braided Copper
Debris Shield Type	Aluminum Foil
EU RoHS Indicator	Yes
Item Type	HDMI Cables
Material - Insulation	30% Glass Filled LCP
Material - Jacket	CM
Sub Brand	iStation
Type	HDMI Cables
UPC	662620212791

Dimensions

Outside Diameter	0.375 in
------------------	----------

Electrical Ratings

Amperage Rating	0.5 A
Current / Amperage Rating	0.5 A
Current Rating	0.5 A
Resistance	30 mili ohms Max
Voltage Rating	40 kV

Conductor Related

Conductor Size	#28 AWG
Conductor Type	Copper
Number Of Conductors	15
Strands	1

Certifications and Compliance

Industry Standard(s)	HDMI
----------------------	------

Logistics

Carton Quantity	12
-----------------	----

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HDC30BK-SPEC-EN | REV 7/2023