



## Cable Assembly, HDMI, #24 AWG, Link, Black, 10'Length

By Bryant  
Catalog # [HDL10BK](#)



Cable Assembly, HDMI, #24 AWG, Link, Black, 10'Length

### General

Braid	Braided Copper
Debris Shield Type	Aluminum Foil
EU RoHS Indicator	Yes
Item Type	HDMI Cables
Material - Insulation	30% Glass Filled LCP
Material - Jacket	CM
Type	HDMI
UPC	662620212708

### Dimensions

Outside Diameter	0.375 in
Weight	0.5 lb

### Electrical Ratings

Amperage Rating	0.5 A
Current / Amperage Rating	0.5 A
Current Rating	0.5 A
Resistance	30 mili ohms Max
Voltage Rating	40 kV

### Conductor Related

Conductor Size	#34 AWG
Conductor Type	Copper
Number Of Conductors	15
Strands	1

### Logistics

Carton Quantity	30
-----------------	----

### Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-HDL10BK-SPEC-EN | REV 7/2023