



Cable Assembly, HDMI, #24AWG, Patch, Black, 3' Length

By Bryant
Catalog # [HDPC03BK](#)



Cable Assembly, HDMI, #24AWG, Patch, Black, 3' Length

Features

- High definition video
- High quality gold connection
- Ideal for audio networking and integration of computer

General

Braid	Braided Copper
Debris Shield Type	Aluminum Foil
EU RoHS Indicator	Yes
Item Type	HDMI Cables
Material - Insulation	30% Glass Filled LCP
Material - Jacket	CM
Type	HDMI
UPC	662620212630

Dimensions

Outside Diameter	0.375 in
Weight	0.25 lb

Electrical Ratings

Amperage Rating	0.5 A
Current / Amperage Rating	0.5 A
Current Rating	0.5 A
Resistance	30 mili ohms Max
Voltage Rating	40 kV

Conductor Related

Conductor Size	#39 AWG
Conductor Type	Copper
Number Of Conductors	15
Strands	1

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalog Page - Bryant R-8 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HDPC03BK-SPEC-EN | REV 7/2023