



Mini-Quick, 4P Coil Cord, 20'

By Bryant
Catalog # [HPMS04C20](#)

Mini-Quick, 4P Coil Cord, 20'



Application

Quick Connect/Disconnect Signal and Control

General

Color	Black
EU RoHS Indicator	Yes
Insulation	SJO
Item Type	Male Straight Plug
Jacket	SJO
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585228778

Dimensions

Diameter Live Part .99"

Conductor Related

Conductor Type Copper
Number Of Conductors 4-Pole

Logistics

Carton Quantity 10

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HPMS04C20-SPEC-EN | REV 7/2023