



## Audio/Video Module, RCA, Solder-Type, 1 Unit, Office White

By Bryant  
Catalog # [IM3RS1W](#)

Audio/Video Module, RCA, Solder-Type, 1 Unit, Office White



### Application

3 RCA Composite Video W/Left Right Audio

### General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION Audio/Video Modules
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	Composite, L/R Audio
Temperature Rating	Per TIA
Type	RCA
UPC	662620849553

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Connectivity	Solder
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

### Logistics

Carton Quantity 25

### Product Assets

[Catalog Page - Bryant R-18 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-IM3RS1W-SPEC-EN | REV 7/2023