



## iStation Module, RCA Audio, 2 RCAs, 110 UTP, 1-Unit, Office White

By Bryant  
Catalog # [IMAR1101OW](#)

iStation Module, RCA Audio, 2 RCAs, 110 UTP, 1-Unit, Office White



### Application

2 RCA Left Right Audio

### General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION Audio/Video Modules
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	Left/Right Audio
Temperature Rating	Per TIA
Type	RCA
UPC	662620858289

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Connectivity	110 Punch Down
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

### Logistics

Carton Quantity 10

### Product Assets

[Catalog Page - Bryant R-18 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-IMAR1101OW-SPEC-EN | REV 7/2023