



Plates, INFINI Module, Component Video, 110 Block, Gray

By Bryant
Catalog # [IMCR1101GY](#)

Plates, INFINI Module, Component Video, 110 Block, Gray



Application

3 RCA Component Video

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION Audio/Video Modules
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	Component
Temperature Rating	Per TIA
Type	RCA
UPC	662620858111

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	110 Punch Down
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity 25

Product Assets

[Catalog Page - Bryant R-18 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-IMCR1101GY-SPEC-EN | REV 7/2023