



# Plate, Decorator Frame, HDMI, 110 Termination, Set, Active, Office White

By Bryant  
Catalog # [ISFH110OW](#)



Plate, Decorator Frame, HDMI, 110 Termination, Set, Active, Office White

## Features

- Locate a display device up to 150' away is as simple as pulling 2 additional UTP cables to a drop
- Terminate with Category 5e, 6 or 6A UTP plenum or non-plenum cable

## Application

HDMI TRAN/RED/DC

## General

Catalog Number	ISFH110OW
Contact	Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION AV Keystone Connections
Material - Mounting Hardware Specifications	Snap-On- Snap-Fit <ul style="list-style-type: none"> <li>• IDC Contact - Phosphor bronze with tin plating over nickel under plating</li> <li>• Material - High impact thermoplastic</li> </ul>

Temperature Rating  
Type  
UPC

- Nose Contact - 19-Pin, Type A, Female Connector, Gold Plated 2u"
- Per TIA  
HDMI  
662620300030

## Dimensions

Display Size 2-Unit

## Electrical Ratings

Connectivity	110 Punch Down Block
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

## Certifications And Compliance

Industry Standard(s) RoHS Compliant

## Logistics

Carton Quantity 25

## Product Assets

[Specifications - ISFH110OW](#)