



## Wallplates and Box Covers, Wallplate, Nylon, 2-Gang, 1) 2.15" Opening, Black

By Bryant  
Catalog # [NP703BK](#)

Double Wallplate, One 2.15" Opening



### Features

- Reinforcement ribs for extra strength
- High-impact, self-extinguishing nylon material
- Captive screw feature holds mounting screw in place
- 1-Single 2.16" (54.9) Diameter Opening

### Application

Protection against contact of live terminals and wiring.  
Provides finished look to installation.

### General

Color	Black
Construction	Molded
Cutout	1) 2.15" Opening, 4-Bolt
EU RoHS Indicator	Yes
Item Type	Screw Mount
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	Standard
Style	1-Single - 2.16 in Hole
Type	Single
UPC	883778103780

### Dimensions

Dimensions	4.63 in x 4.68 in x 0.25 in
Display Size	Standard Sized
Height	0.25 in
Length	4.63 in
Thickness	0.06
Weight	0.06 lb
Width	4.68 in

### Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-NP703BK-SPEC-EN | REV 7/2023