




Plates, 1-Gang, With Jack, 6-Position 4-Conductor, Screw Terminal, White

By Bryant
Catalog # NS730W

Plates, 1-Gang, With Jack, 6-Position 4-Conductor, Screw Terminal, White



General

Application	Communications
Catalog Number	NS730W
Color	White
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) 6-Position 4-Conductor Jack
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice
	Voice
UPC	883778501333

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	3600

Product Assets

- [Catalog Page - PREM S14 CatalogPage](#)
- [Catalog Page - BRY R-13 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - Premise Wiring Catalog](#)



A Hubbell brand