



Plates, 1-Gang, With 2) Jacks, 6-Conductor 4-Position, Screw Terminals, White

By Bryant
Catalog # [NS742W](#)



Plates, 1-Gang, With 2) Jacks, 6- Conductor 4-Position, Screw Terminals, White

Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

Communications

General

Catalog Number	NS742W
Color	Light Almond
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	2) 6-Position 4-Conductor Jack
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	<ul style="list-style-type: none">• Device Type - 6-Position, 4-Conductor• Style - Standard

Temperature Rating

Max Continuous- 75 Degrees C,
Minimum- -40 Without Impact

Type
UPC

Voice
883778501418

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY R-13 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - NS742W](#)