



Plates, 1-Gang, With 2) Jacks, 6-Conductor 4-Position, Screw Terminals, Electric Ivory

By Bryant
Catalog # NS744I



Plates, 1-Gang, With 2) Jacks, 6- Conductor 4-Position, Screw Terminals, Electric Ivory

Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

Communications

General

Catalog Number	NS744I
Color	Ivory
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	2) 6-Position 6-Conductor Jack
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	<ul style="list-style-type: none">• Device Type - 6-Position, 6-Conductor• Style - Standard

Temperature Rating

Max Continuous- 75 Degrees C,
Minimum- -40 Without Impact
Voice

Type
UPC

883778501432

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Connectivity
Contact Resistance
Insertion Loss

Screw Terminals
Per TIA
Per TIA

Certifications And Compliance

Industry Standard(s)

UL Listed

Logistics

Carton Quantity

10

Product Assets

[Catalog Page - BRY R-13 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - NS744I](#)