



1-Gang, Plate with 2) Jacks, 6-Position 6-Conductor, Screw Terminals, White

By Bryant
 Catalog # [NS744W](#)

1-Gang, Plate with 2) Jacks, 6-Position 6-Conductor, Screw Terminals, White



Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

Communications

General

Color	White
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	2) 6-Position 6-Conductor Jack
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice
UPC	883778501449

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant R-13 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.