



Plates, 1-Gang, With F Connector, Jack, 6-Position 4-Conductor, Screw Terminal, White

By Bryant
Catalog # [NS747W](#)

Plates, 1-Gang, With F Connector, Jack, 6-Position 4-Conductor, Screw Terminal, White



Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

Communications

General

Color	<ul style="list-style-type: none"> • White • Blanc
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	6-Position 4-Conductor Jack, 1) F-Coax Connector
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	<ul style="list-style-type: none"> • Voice & CATV • Voice & CATV
UPC	883778501623

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant R-13 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-NS747W-SPEC-EN | REV 7/2023