



Plates, 1-Gang, Mid Sized, With F Connector, Electric Ivory

By Bryant
Catalog # NS751I

Plates, 1-Gang, Mid Sized, With F Connector, Electric Ivory



Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

CATV

General

Catalog Number	NS751I
Color	Ivory
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) F-Coax Connector
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Midsized
Specifications	<ul style="list-style-type: none">• Device Type - Single F-Type• Style - Mid-Size
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact

Type	Voice & CATV
UPC	883778501586

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Female to Female
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY R-13 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - NS751I](#)