



## Plates, 1-Gang, With 2) F Connectors, Electric Ivory

By Bryant  
Catalog # [NS752I](#)



Plates, 1-Gang, With 2) F Connectors, Electric Ivory

### Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

### Application

CATV

### General

Catalog Number	NS752I
Color	Ivory
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	2) F-Coax Connectors
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	<ul style="list-style-type: none"><li>• Device Type - Duplex F-Type</li><li>• Style - Standard</li></ul>

Temperature Rating

Max Continuous- 75 Degrees C,  
Minimum- -40 Without Impact  
Telephone Jack  
883778501555

Type  
UPC

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Connectivity	Female to Female
Contact Resistance	Per TIA
Insertion Loss	Per TIA

### Certifications And Compliance

Industry Standard(s) UL Listed

### Logistics

Carton Quantity 10

### Product Assets

[Catalog Page - BRY R-13 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - NS752I](#)