



Plate Frame with Jack, 6-Position 4-Conductor, Screw Terminal, Gray

By Bryant
Catalog # [NS770GY](#)

Plate Frame with Jack, 6-Position 4- Conductor, Screw Terminal, Gray

Features

- Meets FCC part 68
- High impact-resistant thermoplastic frame

Application

Communications

General

Catalog Number	NS770GY
Color	Gray
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) 6-Position 4-Conductor Jack
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	Device Type - 6-Position, 4-Conductor
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice and Data



UPC 883778501722

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - PREM S13 CatalogPage](#)
[Catalog Page - BRY R-12 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - NS770GY](#)