



**Plates, 1-Gang Frame, With Jack, 6-Position 4-Conductor, Screw Terminal, Light Almond**

By Bryant

Catalog # **NS770LA**

Plates, 1-Gang Frame, With Jack, 6- Position 4-Conductor, Screw  
Terminal, Light Almond



## Features

- Meets FCC part 68
- High impact-resistant thermoplastic frame

## Application

## Communications

## General

Catalog Number	NS770LA
Color	Light Almond/Office White
Construction	Molded
Construction Material - Main	High-Impact Thermoplastic (UL 94V-0)
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) 6-Position 4-Conductor Jack
Material	High-Impact Thermoplastic (UL 94V-0)
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	Device Type - 6-Position, 4-Conductor

### Temperature Rating

Max Continuous- 75 Degrees C,  
Minimum- -40 Without Impact  
Voice and Data  
883778504136

Type  
UPC

## Dimensions

### Display Size

### Standard Sized Product

## Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - PREM S13 CatalogPage](#)  
[Catalog Page - BRY R-12 Catalog Page](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - NS770LA](#)



**A Hubbell brand**