



# Plates, 1-Gang Frame, With Jack, 6-Position 4-Conductor, Screw Terminal, White

By Bryant  
Catalog # [NS770W](#)

Plates, 1-Gang Frame, With Jack, 6- Position 4-Conductor, Screw Terminal, White



## Features

- Meets FCC part 68
- High impact-resistant thermoplastic frame

## Application

Communications

## General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) 6-Position 4-Conductor Jack
Material - Mounting Hardware	Screw Mounting
Size	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	<ul style="list-style-type: none"><li>• Voice and Data</li><li>• Voice and Data</li></ul>
UPC	883778501708

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

## Certifications and Compliance

Industry Standard(s) UL Listed

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - Bryant R-12 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-NS770W-SPEC-EN | REV 7/2023