



Plate Frame with 2) Jacks, 6-Position 6-Conductor, Screw Terminal, White

By Bryant
Catalog # [NS772W](#)



Plate Frame with 2) Jacks, 6-Position 6-Conductor, Screw Terminal, White

Features

- Meets FCC part 68
- High impact-resistant thermoplastic frame

Application

Communications

General

Catalog Number	NS772W
Color	White
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	2) 6-Position 6-Conductor Jack
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	Device Type - 6-Position, 6-Conductor
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact

Type
UPC

Voice and Data
883778501784

Dimensions

Display Size
Standard Sized Product

Electrical Ratings

Connectivity
Contact Resistance
Insertion Loss

Screw Terminals
Per TIA
Per TIA

Certifications And Compliance

Industry Standard(s)
UL Listed

Logistics

Carton Quantity
10

Product Assets

[Catalog Page - BRY R-12 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - NS772W](#)