



Plates, 1-Gang Frame, With F Connector, 6-Position 6-Conductor, Screw Terminal, White

By Bryant
Catalog # [NS783W](#)



Plates, 1-Gang Frame, With F Connector, 6-Position 6-Conductor, Screw Terminal, White

Application

- Communications

General

Catalog Number	NS783W
Color	White
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	2) 6-Position 4-Conductor Jack, 1) F-Coax Connector
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	Device Type - 6-Position, 4-Conductor
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice and Data
UPC	883778501869

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - PREM S13 CatalogPage](#)
[Catalog Page - BRY R-12 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - NS783W](#)