



Plate Frame with F Coax and Cat5e Jack, Brown

By Bryant
Catalog # NS785

Plate Frame with F Coax and Cat5e Jack, Brown



Features

- Meets FCC part 68
- High impact-resistant thermoplastic frame

Application

Communications/CATV

General

Catalog Number	NS785
Color	Brown
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) F-Coax Connector, 1) Cat5e
Material - Mounting Hardware	Screw Mounting
Size	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice and Data
UPC	883778501944

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Female to Female and 110 IDC
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - PREM S13 CatalogPage](#)
[Catalog Page - BRY R-12 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - NS785](#)