



Plate Frame with F Coax and Cat5e Jack, Gray

By Bryant
Catalog # [NS785GY](#)

Plate Frame with F Coax and Cat5e Jack, Gray



Features

- Meets FCC part 68
- High impact-resistant thermoplastic frame

Application

Communications/CATV

General

Color	Gray
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) F-Coax Connector, 1) Cat5e
Material - Mounting Hardware	Screw Mounting
Size	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice and Data
UPC	883778501982

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Female to Female and 110 IDC
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant R-12 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-NS785GY-SPEC-EN | REV 7/2023