



Plate Frame with 1) Cat 5e Jack, 1) 6- Position 4-Conductor Jack and 1) F Coax, Ivory

By Bryant
Catalog # [NS790I](#)

Plate Frame with 1) Cat 5e Jack, 1) 6- Position 4-Conductor Jack and 1) F Coax, Ivory



Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

Communications/CATV

General

| | |
|------------------------------|---|
| Color | Ivory |
| Contact | Phosphor Bronze |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | 1) F-Coax Connector, 1) Cat5e, 1) 6-Position 4-Conductor |
| Material | Nylon |
| Material - Mounting Hardware | Screw Mounting |
| Size | Standard |
| Temperature Rating | Max Continuous- 75 Degrees C, Minimum- -40 Without Impact |
| Type | Voice & CATV |
| UPC | 883778503382 |

Dimensions

Display Size Standard Sized Product

Electrical Ratings

| | |
|--------------------|------------------------------|
| Connectivity | Female to Female and 110 IDC |
| Contact Resistance | Per TIA |
| Insertion Loss | Per TIA |

Certifications and Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant R-13 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-NS790I-SPEC-EN | REV 7/2023