



## Plate Frame with 1) Cat 5e Jack, 1) 6- Position 4-Conductor Jack and 1) F Coax, Light Almond

By Bryant  
Catalog # [NS790LA](#)

Plate Frame with 1) Cat 5e Jack, 1) 6- Position 4-Conductor Jack and 1) F Coax, Light Almond



### Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

### Application

Communications/CATV

### General

Color	Light Almond/Office White
Construction	Molded
Construction Material - Main	High-Impact Thermoplastic (UL 94V-0)
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) F-Coax Connector, 1) Cat5e, 1) 6-Position 4-Conductor
Material	High-Impact Thermoplastic (UL 94V-0)
Material - Mounting Hardware	Screw Mounting
Size	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice & CATV
UPC	883778503399

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Connectivity	Female to Female and 110 IDC
Contact Resistance	Per TIA
Insertion Loss	Per TIA

### Certifications and Compliance

Industry Standard(s) UL Listed

### Logistics

Carton Quantity 10

### Product Assets

[Catalog Page - Bryant R-13 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-NS790LA-SPEC-EN | REV 7/2023