



Decorator Plate Frame with 2) HDMI Female to Female, Ivory

By Bryant
Catalog # NS802I

Decorator Plate Frame with 2) HDMI Female to Female, Ivory



Features

- 4 Inch Flexible Tail Supports Confined Space Applications
- Aesthetically Pleasing, Flush Connector Appearance
- Rear Connector Incorporates Threaded Insert to Secure
- Connection with Hubbell HDMI Cords
- Connector Sized to Fit in 1 Inch Conduit

General

Application	HDMI Decorator Frame Loaded
Color	Ivory
Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION HDMI Extenders and Cables
Material - Mounting Hardware	Snap-On- Snap-Fit
Number Of Ports	2
Temperature Rating	Per TIA
UPC	883778503900

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY R-2 Catalog Page](#)
- [Catalog Page - PREM S4 CatalogPage](#)
- [Catalog Page - PREM F5 CatalogPage](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - Premise Wiring Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-NS802I-SPEC-EN | REV 6/2024