



Wiring Device Kellems, NetSelect, Module Assembly, 6-Voice 1)Data

By Bryant
Catalog # NSO6PIDM

Wiring Device Kellems, NetSelect, Module Assembly, 6-Voice 1)Data



Features

- Meets FCC Part 68 standard
- All data and phone modules 568A wired
- Made of High impact plastic resistant material

Application

Communications

General

Color	Black
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	6) Voice Jacks, 1) Data
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Combination
UPC	883778500435

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Meets FCC Part 68 Standard• RoHS Compliant• UL and cUL Listed
----------------------	---

Logistics

Carton Quantity 10

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-NSO6PIDM-SPEC-EN | REV 7/2023