



Net Select, Module, Multi Pair, Patchable Cord, Multi Mode

By Bryant
Catalog # [NSOMTM24](#)

Net Select, Module, Multi Pair, Patchable Cord, Multi Mode



Application

Telephone

General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Patchable Telcom Multip
Material - Mounting Hardware	Screw Mounting
Style	Telecom
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Telecom
UPC	883778500411

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">Meets FCC Part 68 StandardRoHS CompliantUL and cUL Listed
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant R-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-NSOMTM24-SPEC-EN | REV 7/2023