



Frames, Netselect, Volume Control, Rotary

By Bryant
Catalog # [NSORAVC](#)

Frames, Netselect, Volume Control, Rotary



Application

Analog Audio

General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Rotary Volume Control
Material - Mounting Hardware	Screw Mounting
Style	Audio
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Audio
UPC	883778502958

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• RoHS Compliant• UL and cUL Listed
----------------------	--

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalog Page - Bryant R-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-NSORAVC-SPEC-EN | REV 7/2023