



# Frames, Netselect, Volume Control, Slider

By Bryant  
Catalog # NSOSAVC

Frames, Netselect, Volume Control, Slider



## General

Application	Analog Audio
Catalog Number	NSOSAVC
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Slider Volume Control
Material - Mounting Hardware	Screw Mounting
Style	Audio
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Audio
UPC	883778502941

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

## Certifications And Compliance

Industry Standard(s)	RoHS Compliant UL and cUL Listed
----------------------	-------------------------------------

## Logistics

Carton Quantity	2
-----------------	---

## Product Assets

[Catalog Page - BRY R-7 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand