



Net Select, Module, Combo, Telephone/Cat5e/Video, 6-Port

By Bryant
Catalog # NSOTVDM6

Net Select, Module, Combo, Telephone/Cat5e/Video, 6-Port



Features

- Meets FCC Part 68 standard
- All data and phone modules 568A wired
- Made of High impact plastic resistant material

Application

Combination

General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	6-Port Telephone/Cat5e/Video
Material - Mounting Hardware	Screw Mounting
Style	Combination
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Combination
UPC	883778503948

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Meets FCC Part 68 Standard• RoHS Compliant• UL and cUL Listed
----------------------	---

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant R-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-NSOTVDM6-SPEC-EN | REV 7/2023