



# Net Select, Module, Combo, Telephone/Video, 6-Port

By Bryant  
Catalog # [NSOTVM6](#)

Net Select, Module, Combo, Telephone/Video, 6-Port



## Features

- Meets FCC Part 68 standard
- All data and phone modules 568A wired
- Made of High impact plastic resistant material

## Application

Combination

## General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	6-Port Telephone/Video
Material - Mounting Hardware	Screw Mounting
Style	Combination
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Combination
UPC	883778503931

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Meets FCC Part 68 Standard</li><li>• RoHS Compliant</li><li>• UL and cUL Listed</li></ul>
----------------------	---

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - Bryant R-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-NSOTVM6-SPEC-EN | REV 7/2023