



## Net Select, Module, 4-Way Coax, 2.3GHz, Plastic

By Bryant  
Catalog # NSOVM42G

Net Select, Module, 4-Way Coax, 2.3GHz, Plastic



### Features

- Made of High impact plastic resistant material
- Pre-mounted push pins snap the module quickly into place

### Application

CATV

### General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	4-Way Coax, 2.3GHz
Material - Mounting Hardware	Screw Mounting
Style	Coaxial Splitter
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	<ul style="list-style-type: none"><li>• Coaxial Splitter</li><li>• Coaxial Splitter</li></ul>
UPC	883778504372

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

### Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• RoHS Compliant</li><li>• UL and cUL Listed</li></ul>
----------------------	--

### Product Assets

[Catalog Page - Bryant R-5 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-NSOVM42G-SPEC-EN | REV 7/2023