



Net Select, Module, 6-Way Coax, 2.3GHz, Plastic

By Bryant

Catalog # [NSOVM62G](#)



Net Select, Module, 6-Way Coax, 2.3GHz, Plastic

General

Application	CATV
Catalog Number	NSOVM62G
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	6-Way Coax, 2.3GHz
Material - Mounting Hardware	Screw Mounting
Style	Coaxial Splitter
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Coaxial Splitter
UPC	883778504396

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	RoHS Compliant
	UL and cUL Listed

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY R-5 Catalog Page](#)
- [Catalog Page - PREM S8 CatalogPage](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - Premise Wiring Catalog](#)



A Hubbell brand