



Net Select, Module, 8-Way Coax, 1GHz, Plastic

By Bryant
Catalog # NSOVM8



Net Select, Module, 8-Way Coax, 1GHz, Plastic

Application

CATV

General

Catalog Number	NSOVM8
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	8-Way Coax, 1GHz
Material - Mounting Hardware	Screw Mounting
Specifications	<ul style="list-style-type: none">• Dimensions - 6.47 in. W x 2.09 in. H x 3.20 in. D• Material - High impact plastic
Style	Coaxial Splitter
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Coaxial Splitter
UPC	883778504402

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• RoHS Compliant• UL and cUL Listed
----------------------	--

Logistics

Carton Quantity	10
Pallet Quantity	750

Product Assets

- [Catalog Page - PREM S8 CatalogPage](#)
- [Catalog Page - BRY R-5 Catalog Page](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - NSOVM8](#)



A Hubbell brand